


Typical Saturation Efficiency (45/45) 5mm Flute Height




FACE VELOCITY (FPM) →		200	250	300	350	400	450	500	550	600
PAD THICKNESS	M/S →	1	1.25	1.5	1.75	2	2.25	2.5	2.75	3
	50mm (2")	74	73	71	69	68	66	64	62	59
	60mm (2.36")	84	82	80	79	77	75	73	71	69
	75mm (3")	89	88	86	85	83	82	80	78	76
	100mm (4")	95	94	92	91	89	88	86	85	83

Rev. 01
Document No- ECP-305-R0

Pressure Drop Across Media (45/45)

5mm Flute Height



FACE VELOCITY (FPM) →		200	250	300	350	400	450	500	550	600
PAD THICKNESS	M/S →	1	1.25	1.5	1.75	2	2.25	2.5	2.75	3
	2"/50mm	0.7	1.0	1.3	1.7	2.0	2.5	3.0	3.6	4.2
	2.36"/60mm	0.8	1.2	1.6	2.0	2.4	3.0	3.6	4.3	5.0
	3"/75mm	1.1	1.6	2.1	2.7	3.2	3.9	4.6	5.4	6.2
	4"/100mm	2.0	2.5	2.9	3.5	4.1	5.3	6.5	8.1	9.6